



Addigy® F1030 CF10

Fused Filament Fabrication



Addigy® F1030 CF10 is a new polyamide for 3D printing parts with properties close to what is usually achievable only by injection molding. With a loading of 10% carbon fiber, it produces stronger, tougher and stiffer 3D printed parts while it can be printed at the same speeds as unreinforced plastics.

Addigy® F1030 CF10 is a new carbon fiber filled PA6/66 copolymer filament for 3D printing durable structural parts with high dimensional stability, warpage free. Filled with only 10% of actual carbon fiber – much lower than most carbon filled materials – **Addigy® F1030 CF10** enables parts that are stronger, stiffer and tougher parts with higher tensile strength and modulus.

Designed especially for 3D printing, its excellent mechanical properties and smooth appearance make it ideal for demanding automotive structural applications that require robust performance at elevated temperatures.

The material can be printed on standard desktop fused filament fabrication (FFF) machines with a hardened nozzle. Tests have shown that users can run their printers at the same speeds as with unreinforced plastics, while achieving considerably better strength and toughness.

Key Benefits

- 3D printable at same speed as unreinforced plastics thanks to low carbon loading of 10%
- Enables properties close to what is usually achievable only by injection molding
- Durable parts with good mechanical properties due to high inter-layer strength
- Made from Covestro **Addigy®** copolyamide PA6/66, which is used in automotive and electronics for many years
- HDT of 184°C at 1.8 MPa
- Very low warpage compared to unfilled PA
- Characteristic matte black surface-finish with less roughness

Ideal Applications

- Automotive under-the-hood applications
- Protective and supporting sports gear
- High performance functional parts
- Manufacturing jigs and fixtures
- Medical braces and prosthetics
- Light weight applications
- Applications requiring durable and stiff parts with good mechanical properties

Technical Data

Properties	Typical Data	Unit	Test method
Mechanical Properties (Injection Molded)	dry / cond		
Tensile modulus	7,570 / –	MPa	ISO 527-1/-2
Yield stress	110 / –	MPa	ISO 527-1/-2
Yield strain	2.8 / –	%	ISO 527-1/-2
Stress at break	110 / –	MPa	ISO 527-1/-2
Strain at break	3 / –	%	ISO 527-1/-2

Mechanical properties	Value	Unit	Test Method
Tensile modulus (3D printed: flat X-X direction)	7,630	MPa	ISO 527-1/-2
Stress at yield (3D printed: flat X-X direction)	110	MPa	ISO 527-1/-2
Strain at yield (3D printed: flat X-X direction)	2.5	%	ISO 527-1/-2
Stress at break (3D printed: flat X-X direction)	110	MPa	ISO 527-1/-2
Strain at break (3D printed: flat X-X direction)	2.2	%	ISO 527-1/-2
Tensile modulus (3D printed: flat Y-X direction)	2,720	MPa	ISO 527-1/-2
Stress at yield (3D printed: flat Y-X direction)	63	MPa	ISO 527-1/-2
Stress at yield (3D printed: flat Y-X direction)	3	%	ISO 527-1/-2
Stress at break (3D printed: flat Y-X direction)	58	MPa	ISO 527-1/-2
Strain at break (3D printed: flat Y-X direction)	4.5	%	ISO 527-1/-2

Thermal Properties	Dry / Cond	Unit	Test Method
Melting temperature (10°C/min)	200 / –	°C	ISO 11357-1/-3
Glass transition temperature (10°C/min)	58 / –	°C	ISO 11357-1/-2
Temp. of defl ection under load (1.80 MPa)	153 / –	°C	ISO 75-1/-2
Temp. of defl ection under load (0.45 MPa)	184 / –	°C	ISO 75-1/-2

Other Properties	Dry / Cond	Unit	Test Method
Density	1,170 / –	kg/m ³	ISO 1183

These values may vary and depend on individual machine processing and post-curing practices.

More information at am.covestro.com



Covestro Deutschland AG
Kaiser-Wilhelm-Allee 60
51373 Leverkusen
Germany

www.covestro.com

The manner in which you use our products, technical assistance and information (whether verbal, written or by way of production evaluations), including any suggested formulations and recommendations, is beyond our control. Therefore, it is imperative that you test our products to determine suitability for your processing and intended uses. Your analysis must at least include testing to determine suitability from a technical, health, safety, and environmental and regulatory standpoint. Such testing has not necessarily been done by Covestro, and Covestro has not obtained any approvals or licenses for a particular use or application of the product, unless explicitly stated otherwise. If the intended use of the product is for the manufacture of a pharmaceutical/medicinal product, medical device¹ or of pre-cursor products for medical devices or for other specifically regulated applications which lead or may lead to a regulatory obligation of Covestro, Covestro must explicitly agree to such application before the sale. Any samples provided by Covestro are for testing purposes only and not for commercial use. Unless we otherwise agree in writing, all products are sold strictly pursuant to the terms of our standard conditions of sale which are available upon request. All information, including technical assistance is given without warranty or guarantee and is subject to change without notice. It is expressly understood and agreed by you that you assume and hereby expressly release and indemnify us and hold us harmless from all liability, in tort, contract or otherwise, incurred in connection with the use of our products, technical assistance, and information. Any statement or recommendation not contained herein is unauthorized and shall not bind us. Nothing herein shall be construed as a recommendation to use any product in conflict with any claim of any patent relative to any material or its use. No license is implied or in fact granted under the claims of any patent. For more information on Covestro products in Medical Applications, please request from your sales support contact our Guidance document: GUIDANCE ON USE OF COVESTRO PRODUCTS IN A MEDICAL APPLICATION. These values are typical values only. Unless explicitly agreed in written form, they do not constitute a binding material specification or warranted values. The biocompatibility testing referenced above cannot assure the biocompatibility of final or intermediate products made from Covestro products or the suitability of such products for their use in a medical application, i.e., the test data cannot be used to conclude that any medical devices manufactured from the Covestro products meet the necessary requirements of ISO Standard 10993-1. It is the sole responsibility of the manufacturer of the final end-use product to conduct all necessary tests (including biocompatibility tests) and inspections and to evaluate the final product under actual end-use requirements.

¹Please see the "Guidance on Use of Covestro Products in a Medical Application" document.
Edition: April 2022 · Printed in Germany